
## Optically Coupled Isolator / High-Speed Optically Coupled Isolator OPI150, OPI153, OPI155



## Features:

- 50 kV electrical isolation
- Choice of phototransistor or photodarlington output
- High speed >5 MBd (OPI155)
- Hermetically sealed LED and photosensor
- Base contact lead for conventional transistor biasing
- TX and TXV process available (see Hi-Rel section)




### **Description:**

Each **OPI150** and **OPI153** is an optically coupled isolator that contains an infrared emitting diode and a NPN silicon phototransistor (OPI150) or photodarlington (OPI153), each sealed in an individual hermetically sealed package. The diode and phototransistor or diode and photodarlington are then optically coupled by means of a light pipe and mounted in a high dielectric plastic housing. These devices are designed for applications that require very high isolation between input and output.

The **OPI155** is a high-speed optical coupled isolator that contains a high speed monolithic photo-IC comprised of a photodiode and a DC amplifier that drives an open collector output Schottky transistor. It is optically coupled by means of an internal light pipe. The LED and sensor are both in separate hermetically sealed packages that are then mounted in a high dielectric plastic housing. This device is designed for applications that require high speed *and* high voltage isolation between the input and output.

TX and TXV devices are available. Please contact your local representative or OPTEK for more information.



## Optically Coupled Isolator / High-Speed Optically Coupled Isolator OPI150, OPI153, OPI155



<b>Absolute Maximum Ratings</b> ( $T_A = 25^\circ$ C unless otherwise noted)	
Operating Temperature Range	-40° C to +85° C
Storage Temperature Range	-40° C to +85° C
Input-to-Output Isolation Voltage <sup>(1)(2)</sup>	±50 kVDC
Lead Soldering Temperature [1/16 inch (1.6 mm) from the case for 5 seconds with soldering iron <sup>1(3)</sup>	260° C
Input Diode	
Continuous Forward Current	50 mA
Reverse Voltage	3 V
Power Dissipation <sup>(4)</sup>	200 mW
Output Phototransistor or Photodarlington (OPI150, OPI153)	
Collector-Base Voltage OPI150 OPI153	30 V 20 V
Collector-Emitter Voltage OPI150 OPI153	30 V 15 V
Emitter-Collector Voltage	5.0 V
Power Dissipation <sup>(5)</sup>	250 mW

#### **Output Photosensor (OPI155)**

Supply Voltage	-0.5 to 7 V
Output Voltage	-0.5 to 18 V
Output Current	25 mA
Open-Collector Power Dissipation	40 mW
Power Dissipation <sup>(5)</sup>	250 mW

Notes:

(1) For OPI150 and OPI153, measured with input leads and output leads shorted.

(2) For OPI155, measured with input and output leads shorted and relative humidity of less than 50%.

(3) RMA flux is recommended. Duration can be extended to 10 seconds maximum when flow soldering.

(4) Derate linearly 3.33 mW/° C above 25° C.

(5) Derate linearly 4.17 mW/° C above 25° C.

#### Electrical Characteristics (T<sub>A</sub> = 25° C unless otherwise noted)

SYMBOL	PARAMETER	MIN	TYP	MAX	UNITS	TEST CONDITIONS
--------	-----------	-----	-----	-----	-------	-----------------

**Input Diode** (For OPI150 & OPI153, see OP236 for additional information - for reference only. For OPI155, see OP235W for additional information - for reference only.)

V <sub>F</sub>	Forward Voltage OPI150, OPI153 OPI155	-	1.3 1.2	1.6 1.6	V	I <sub>F</sub> = 50 mA I <sub>F</sub> = 10 mA
I <sub>R</sub>	Reverse Current	-	0.1	100	μA	V <sub>R</sub> = 3 V

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.

## Optically Coupled Isolator / High-Speed Optically Coupled Isolator OPI150, OPI153, OPI155



SYMBOL	PARAMETER	MIN	TYP	MAX	UNITS	TEST CONDITIONS
	ototransistor or Photodarlington (For a linformation- for reference only.)	OPI150	, see O	P805SL	for additi	onal information, for OPI153, see OP830S
$V_{(BR)C\textbf{E}\textbf{0}}$	Collector-Emitter Breakdown Voltage OPI150 OPI153	30 15	-	-	v	I <sub>C</sub> = 1 mA
V <sub>(BR)ECO</sub>	Emitter-Collector Breakdown Voltage OPI150, OPI153	5	-	-	v	Ι <sub>F</sub> = 100 μΑ
V <sub>(BR)CBO</sub>	Collector-Base Breakdown Voltage OPI150 OPI153	30 20	- -		v	I <sub>C</sub> = 100 μA
I <sub>CEO</sub>	Collector-Emitter Dark Current OPI150 OPI153	-	- -	100 500	nA	V <sub>CE</sub> = 10 V
I <sub>CBO</sub>	Collector-Base Dark Current OPI150	-	-	-	nA	V <sub>CB</sub> = 10 V
Coupled (	OPI150, OPI153)			•	•	
I <sub>C/</sub> I <sub>F</sub>	DC Current Transfer Ratio OPI150 OPI153	10 25	-	-	%	I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 5 V I <sub>F</sub> = 20 mA, V <sub>CE</sub> = 5 V
I <sub>CB(ON)</sub>	Ib0State Photodiode Current OPI150	10	-	-	μA	I <sub>F</sub> = 20 mA, V <sub>CB</sub> = 5 V
V <sub>CE(SAT)</sub>	Saturation Voltage OPI150 OPI153		-	0.5 1.2	V	I <sub>F</sub> = 16 mA, I <sub>C</sub> = 1 mA I <sub>F</sub> = 30 mA, I <sub>C</sub> = 2 mA
Output Ph	otosensor (OPI155)					
I <sub>OH</sub>	High Level Output Current OPI155	-	_	250	μA	$V_{O}$ = 18 V, I <sub>F</sub> = 0, $V_{CC}$ = Open
I <sub>CCH</sub>	High Level Supply Current OPI155	-	-	6.5	mA	$V_{CC}$ = 5.25 V, I <sub>F</sub> = 0, V <sub>O</sub> = Open
I <sub>CCL</sub>	Low Level Supply Current OPI155	-	-	10	mA	$V_{CC}$ = 5.25 V, I <sub>F</sub> = 10 mA, V <sub>O</sub> = 0
V <sub>OL</sub>	Low Level Output Voltage OPI155	-	-	0.5	V	V <sub>CC</sub> = 5.25 V, I <sub>F</sub> = 10 mA, I <sub>O</sub> = 8 mA
Switching	Characteristics (OPI155)	· ·			•	•
T <sub>PHL</sub>	Propagation Delay, High to Low	-	120	150		
T <sub>PLH</sub>	Propagation Delay, Low to High	-	70	100	ns	$V_{CC} = 5 \text{ V}, \text{ I}_{\text{F}} = 10 \text{ mA}, \text{ R}_{\text{L}} = 360 \Omega$

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Optek: OPI155 OPI153

TT electronics: OPI150